




PANDUIT PART NO. *	BUNDLE DIA.		A	B	C	D	E	F	G	H	J	MAX. PANEL THICKNESS	MIN. LOOP TENSILE	CROSS SECTION	WEIGHT
	MIN. in (mm)	MAX. in (mm)													
PRWP2H	.188 (4.8)	2.00 (50.8)	.075 (1.9)	.300 (7.6)	.300 (7.6)	.370 (9.4)	.480 (12.2)	8.9 (226)	.416 (10.6)	.266 (6.8)	.740 (18.8)	.105 (2.7)	120 (534)	HEAVY	.86 (390)

NOTE:

- * 1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR.

DIMENSIONS IN PARENTHESIS ARE IN METRIC UNITS

PANDUIT CORP. TINLEY PARK, ILLINOIS

RELEASABLE WING PUSH MOUNT TIE
PRWP2H

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± .1(.25) (.XXX) ± .020(.51)
(.XX) ± .02(.5) ANGLES ± -----

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY
RAM

MAT'L:

SCALE .8:1

DATE
7-28-93NYLON
6/6DRAWING NO.
SS-26837DWG
A
SIZECHK'D
HVP

4	1/29/04	JABO		CHANGED FORMAT FOR CONSISTENCY SEE ECN FOR DETAILS			26837	4							
REV	DATE	BY	CHK	DESCRIPTION			ECN	R	CUST	SUP					