


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO.	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	MIN. LOOP* TENSILE lbs. (N)	ROLL DESCRIPTION	APPROXIMATE WEIGHT lbs/10 ROLLS (g)
	MIN. in (mm)	MAX. in (mm)						
HLS1.5S	.25 (6.4)	1.5 (38.1)	.100 (2.5)	6.0 (152)	.750 (19.1)	50 (222)	PERFORATED STRIPS QTY: 10 PIECES/ROLL	.43 (194)
HLS3S	.25 (6.4)	3.2 (81.3)	.100 (2.5)	12.0 (305)	.750 (19.1)	50 (222)		.85 (384)
HLS5S	.25 (6.4)	5.0 (127)	.100 (2.5)	18.0 (457)	.750 (19.1)	50 (222)		1.25 (568)
HLS-15R	.25 (6.4)	VARIOUS	.100 (2.5)	180 (4572)	.750 (19.1)	50 (222)	15 FT CONTINUOUS	1.25 (567)
HLS-75R	.25 (6.4)	VARIOUS	.100 (2.5)	900 (22860)	.750 (19.1)	50 (222)	75 FT	6.32 (2867)




ILLUSTRATION 'A'

NOTES:

- 1) ALL LENGTHS PACKED IN ROLL FORM (SEE ILLUSTRATION 'A')
- \* 2) MINIMUM 2" OVERLAP REQUIRED TO ACHIEVE LOOP TENSILE RATING.
- 3) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR OPTIONAL COLORS.

DIMENSIONS IN PARENTHESIS ARE IN METRIC UNITS

SS-27184.prt

PANDUIT CORP. TINLEY PARK, ILLINOIS

TAK-TY HOOK & LOOP CABLE TIES  
HLS SERIES

UNLESS OTHERWISE SPECIFIED,  
DIMENSIONAL TOLERANCES ARE:  
(.X) ± (.XXX) ± .035  
(.XX) ± ANGLES ±

UNLESS OTHERWISE SPECIFIED,  
ALL DIMENSIONS ARE GIVEN  
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY  
KET

MAT'L:

SCALE NONE

DATE  
12/30/98

POLYETHYLENE HOOK/  
NYLON LOOP

DRAWING NO.

SS-27184

DWG  
A  
SIZE

4	6/5/06	FAB		ADDED PART WEIGHTS TO DRAWING	27184	4				
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP		

CHK'D  
HVP