


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO. *	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	MIN. LOOP TENSILE LBS. (N)	CROSS SECTION	TIP STYLE	WEIGHT lbs/100 pcs. (g)
	MIN. in (mm)	MAX. in (mm)										
1LT2S	.188 (4.8)	1.88 (47.8)	.052 (1.3)	.190 (4.8)	.389 (9.9)	.140 (3.6)	.316 (8.0)	8.30 (211)	50 (222)	STANDARD	CURVED	.284 (129)
1LT3S	.188 (4.8)	3.00 (76.2)	.052 (1.3)	.190 (4.8)	.389 (9.9)	.140 (3.6)	.316 (8.0)	11.5 (292)	50 (222)	STANDARD	CURVED	.385 (175)
1LT4S	.188 (4.8)	4.00 (101.6)	.052 (1.3)	.190 (4.8)	.389 (9.9)	.140 (3.6)	.316 (8.0)	14.7 (373)	50 (222)	STANDARD	CURVED	.490 (222)
1LT4LH	.200 (5.1)	4.00 (101.6)	.075 (1.9)	.300 (7.6)	.600 (15.2)	.250 (6.4)	.515 (13.1)	14.8 (376)	120 (534)	LIGHT HEAVY	CURVED	1.132 (514)
1LT6LH	.200 (5.1)	6.00 (152.4)	.075 (1.9)	.300 (7.6)	.600 (15.2)	.250 (6.4)	.515 (13.1)	21.2 (538)	120 (534)	LIGHT HEAVY	CURVED	1.610 (731)

NOTE :

SEE WWW.PANDUIT.COM FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR.

W10001BZ/08-SS-27217.PRT

										DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS			
										PANDUIT CORP. TINLEY PARK, ILLINOIS			
										BELT-TY INLINE-TIE CABLE TIES ILT SERIES			
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .--- (.XXX) ±.020(.51) (.XX) ±.02(.5) ANGLES ± .---		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
---	---	---		ADDED WWW.PANDUIT.COM NOTE	---	---				DRAWN BY CJW	MAT'L; NYLON 6.6	SCALE NONE	
8	8/18/08	JABO		ADDED MATERIAL IN TITLE BLOCK	27217	8				DATE 6-9-99		DRAWING NO. SS-27217	DWG A
REV	DATE	BY	CHK	DESCRIPTION	ECN	-	R	CUST	SUP	CHK'D JKG		SIZE	