


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	LENGTH	WEIGHT
T70DW6	72.00 ±.18 (1829 ±4.6)	.44 LB/72 IN (200 G/1829 mm)
T70DW8	96.00 ±.18 (2438 ±4.6)	.59 LB/96 IN (268 G/2438 mm)
T70DW10	120.00 ±.18 (3048 ±4.6)	.73 LB/120 IN (332 G/3048 mm)
T70DW2	78.7 ±.18 (2000 ±4.6)	.48 LB/78.7 IN (218 G/2000 mm)



- NOTES:
- SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
 - THE T70DW SNAPS ONTO RAILS IN THE T70 RACEWAY BASE TO CREATE SEPARATE CHANNELS.
 - DIMENSIONS IN PARENTHESIS ARE IN METRIC.

CAD FILENAME/LAYERS										D35541CB_DC_T70DW_02A.PRT									
PANDUIT										CORP. TINLEY PARK, ILLINOIS									
T70 RACEWAY DIVIDER WALL (T70DW6, T70DW8, T70DW10, T70DW2)										CUSTOMER DRAWING									
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ±.010(.3) (.XX) ±.03(.8) ANGLES ±										UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.									
DRAWN BY										MAT'L:									
JBA										NONE									
DATE										DRAWING NO.									
09-19-96										PVC									
CHECKED BY										35541-28									
CEF										A									
REV										SIZE									
DATE																			
BY																			
CHK																			
DESCRIPTION																			
ECN																			
CHK																			
CUST																			
SUP																			