



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
T70N4	.06 LB/10 PCS (27g/10 PCS)

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. DIMENSIONS IN PARENTHESES ARE IN METRIC.



CAD FILENAME/LAYERS D37352BA_DC_T70N4_04A.PRT

PANDUIT CORP. TINLEY PARK, ILLINOIS

T70 4 POSITION HORIZONTAL
MDVO FACEPLATE (T70N4)
CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± (.XXX) ±
(.XX) ±.03(.8) ANGLES ±

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY
JHNU

MAT'L:

SCALE
NONE

DATE
8-28-00

DRAWING NO.
37352-08

DRG

CHECKED BY
SMF

SIZE
A

REV	DATE	BY	CHK	DESCRIPTION	ECN	CHK	CUST	SUP
R	8-26-00	JHNU	SMF	RELEASED TO PRODUCTION.	37352-08	HIW	HIW	