



PERFORMANCE SPECIFICATION

TESTING	MINIMUM	TEST METHODS
PEEL STRENGTH	0.30 POUNDS PER INCH WIDTH	40011
MECHANICAL STRENGTH	18 LB PER 0.75 SQUIRE INCHES	UL1565
FLAMMABILITY-20MM	AFTER FLAME TIME INDIVIDUAL $\leq 30s$	UL94-V2 RATING
VERTICAL BURN	TOTAL AFTER FLAME TIME ANY CONDITION $\leq 250s$	
	AFTER FLAME PLUS AFTERGLOW INDIVIDUAL AFTER SECOND FLAME $\leq 60s$	

<p>*** NOTICE ***</p> <p>THIS DOCUMENT CONTAINS CONFIDENTIAL AND/OR PROPRIETARY INFORMATION INTENDED FOR USE ONLY BY THE INDIVIDUAL(S) SPECIFIED HEREIN AND ONLY FOR THE PURPOSE(S) PROVIDED. NEITHER THIS DOCUMENT, NOR ANY INFORMATION CONTAINED HEREIN, MAY BE COPIED, DISTRIBUTED, DISCLOSED TO ANY THIRD PARTY OR USED IN ANY MANNER OTHER THAN FOR WHICH IT HAS BEEN PROVIDED, WITHOUT THE PRIOR WRITTEN CONSENT OF ORTRONICS, INC.</p>		<p>ORTRONICS®</p> <p>NEW LONDON, CT 06320 (860) 445-3800</p>		<p>TITLE</p> <p>PLEN-TIE, PLENUM HOOK-LOOP STRAPS 1/2" x 8", CRANBERRY, ROLL OF 20</p>	
DWN.BY:	S. LEVESQUE	DATE	02/05/04	SIZE	CAD FILE
CHK.BY:				A	70700143C
APP.BY:				SCALE	NONE
				DATE	03/23/04
				SHEET	1 OF 1
				PART NUMBER	OR-70700143
				REV	01