

Product Cut Sheet

MCS MASTER CABLING SECTION

The MCS Master Cabling Section virtually eliminates the need for horizontal cable managers by providing frequent 1U spacing of the cable guides that aligns precisely with the rack spacing.

Includes innovative, rigid aluminum SwitchGate Door/Cover that hides and conceals cable. A handle is included on the outside of the door/cover, making removal and installation even easier.

- Extra-wide, contoured cable guides provide smooth movement and meet UL 94V-0 Flame Resistant standards
- SwitchGate Door/Cover is easily switched from right to left opening and can be removed
- Double-Sided MCS Master Cabling Sections have edge-protected pass through ports and vertical slots for optional Saf-T-Grip® straps
- 10"W (250 mm) version includes (4) Cable Distribution Spools
- Mounting hardware and doors are included
- Attach to Standard Racks, Universal Racks or QuadraRacks



Double-Sided MCS shown with door open



Part Number	Height ft (m)	Depth in (mm)	Shipping Weight lb (kg)
4.4"W (112 mm) Single-Sided			
30091-X00	5.6 (1.7)	8.08 (205.2)	14 (6.4)
30091-X01	6 (1.8)	8.08 (205.2)	15 (6.8)
30091-X02	6.6 (2.0)	8.08 (205.2)	16 (7.3)
30091-X03	7 (2.1)	8.08 (205.2)	17 (7.7)
30091-X05	7.6 (2.3)	8.08 (205.2)	18 (8.2)
30091-X15	8 (2.4)	8.08 (205.2)	20 (9.1)
30091-X08	9 (2.7)	8.08 (205.2)	22 (10.0)
6"W (150 mm) Single-Sided			
30092-X00	5.6 (1.7)	8.08 (205.2)	16 (7.3)
30092-X01	6 (1.8)	8.08 (205.2)	17 (7.7)
30092-X02	6.6 (2.0)	8.08 (205.2)	19 (8.6)
30092-X03	7 (2.1)	8.08 (205.2)	20 (9.1)
30092-X05	7.6 (2.3)	8.08 (205.2)	21 (9.5)
30092-X15	8 (2.4)	8.08 (205.2)	23 (10.4)
30092-X08	9 (2.7)	8.08 (205.2)	25 (11.3)
10"W (250 mm) Single-Sided			
30093-X00	5.6 (1.7)	8.08 (205.2)	38 (17.2)
30093-X01	6 (1.8)	8.08 (205.2)	40 (18.1)
30093-X02	6.6 (2.0)	8.08 (205.2)	43 (19.5)
30093-X03	7 (2.1)	8.08 (205.2)	45 (20.4)
30093-X05	7.6 (2.3)	8.08 (205.2)	48 (21.8)
30093-X15	8 (2.4)	8.08 (205.2)	51 (23.1)
30093-X08	9 (2.7)	8.08 (205.2)	56 (25.4)

Part Number	Height ft (m)	Depth in (mm)	Shipping Weight lb (kg)
4.4"W (112 mm) Double-Sided			
30094-X00	5.6 (1.7)	16.15 (410.2)	34 (15.4)
30094-X01	6 (1.8)	16.15 (410.2)	36 (16.3)
30094-X02	6.6 (2.0)	16.15 (410.2)	38 (17.2)
30094-X03	7 (2.1)	16.15 (410.2)	40 (18.1)
30094-X05	7.6 (2.3)	16.15 (410.2)	42 (19.1)
30094-X15	8 (2.4)	16.15 (410.2)	45 (20.4)
30094-X08	9 (2.7)	16.15 (410.2)	49 (22.2)
6"W (150 mm) Double-Sided			
30095-X00	5.6 (1.7)	16.15 (410.2)	38 (17.2)
30095-X01	6 (1.8)	16.15 (410.2)	40 (18.1)
30095-X02	6.6 (2.0)	16.15 (410.2)	43 (19.5)
30095-X03	7 (2.1)	16.15 (410.2)	45 (20.4)
30095-X05	7.6 (2.3)	16.15 (410.2)	48 (21.8)
30095-X15	8 (2.4)	16.15 (410.2)	51 (23.1)
30095-X08	9 (2.7)	16.15 (410.2)	56 (25.4)
10"W (250 mm) Double-Sided			
30096-X00	5.6 (1.7)	16.15 (410.2)	44 (20.0)
30096-X01	6 (1.8)	16.15 (410.2)	47 (21.3)
30096-X02	6.6 (2.0)	16.15 (410.2)	50 (22.7)
30096-X03	7 (2.1)	16.15 (410.2)	53 (24.0)
30096-X05	7.6 (2.3)	16.15 (410.2)	57 (25.9)
30096-X15	8 (2.4)	16.15 (410.2)	60 (27.2)
30096-X08	9 (2.7)	16.15 (410.2)	67 (30.4)

X=Color; 5=Clear, 7=Black, E=Glacier White. Clear (-5XX) versions have black doors/covers and cable guides.
9' (2.7 m) unit is an 8' (2.4 m) unit with 1' (0.3 m) extension.

800-834-4969 in U.S. & Canada • www.chatsworth.com



CHATSWORTH PRODUCTS

©2013 Chatsworth Products, Inc. All rights reserved. CPI, CPI Passive Cooling, GlobalFrame, MegaFrame, Saf-T-Grip, Seismic Frame, SlimFrame, TeraFrame, Cube-iT Plus, Evolution, OnTrac, Velocity and QuadraRack are federally registered trademarks of Chatsworth Products. eConnect and Simply Efficient are trademarks of Chatsworth Products. All other trademarks belong to their respective companies. Rev.3 07/13