

19” 1U Fan Module



Operating Voltage AC 220 - 240 Volts 50/60 Hz  
Standards Conforms to IEC 297-1 Air Flow 95 -115 CFM  
Noise 44 - 49 dB (A) Material 1,5 mm Steel  
Fan Speed 2700 - 3100 rpm Finish Electrostatic Powder Paint  
Packaging One piece in a box

H (mm)	D (mm)	W (mm)	Number of Fans	Weight kg	Part No
1U	258	483	3	4,19	CCA-X-2001

\* X : Color code = 7: RAL 7035 (Grey); 9: RAL 9005 (Black)