RRF Full-Hole Rackrail

GREENGUARD EIA/TIA Compliant

Features

- Tapped for 10-32 threads
- Threaded rack rail is 1/8" [3mm] thick


Middle Atlantic Products

EXCEPTIONAL SUPPORT & PROTECTION"

- Suitable for use in 19-1/8" [486mm] wide openings
- Sold in pairs



RRF basic dimensions



PART #	I FNGTH	RACKING HFIGHT	MATERIAI
RRF2	3.50″	(2 spaces)	0.125" steel
RRF4	7.00″	(4 spaces)	0.125" steel
RRF6	10.50″	(6 spaces)	0.125″ steel
RRF8	14.00″	(8 spaces)	0.125" steel
RRF12	21.00″	(12 spaces)	0.125" steel
RRF14	24.50″	(14 spaces)	0.125" steel
RRF16	28.00″	(16 spaces)	0.125″ steel
RRF18	31.50″	(18 spaces)	0.125″ steel
RRF21	36.75″	(21 spaces)	0.125″ steel
RRF27	47.25″	(27 spaces)	0.125" steel
RRF45	78.75″	(45 spaces)	0.125″ steel

Architects' and Engineers' Specifications

EIA/TIA compliant RRF Series Rackrail shall be Middle Atlantic Products model number RRFx (refer to chart). Rackrail shall be 1/8" thick steel. Rail shall be <u>x</u> rackspaces in length (refer to chart) pre-treatment process shall be 3 stage iron phosphate. Steel rackrail shall be finished with a durable black e-coat. Rackrail shall be GREENGUARD Indoor Air Quality Certified for Children and Schools. Rackrail shall be RoHS EU Directive 2002/95/EC compliant. Rackrail shall be manufactured by an ISO 9001 and ISO 14001 registered company. Rackrail shall be warrantied to be free from defects in material or workmanship under normal use and conditions for the lifetime of the product.

CUSTOMIZABLE SPECIFICATION CLIPS AVAILABLE AT MIDDLEATLANTIC.COM

US: New Jersey • California • Illinois • Voice: 973-839-1011 Fax: 973-839-1976 • middleatlantic.com Canada: Ontario • British Columbia • Voice: 613-836-2501 Fax: 613-836-2690 • middleatlantic.ca