



C240-QMRQMR

CNT-240 CNT® Jumper with interface types QMA Male Right Angle and QMA Male Right Angle, variable length

## General Specifications

Body Style, Connector A	Right angle
Body Style, Connector B	Right angle
Cable Family	CNT-240
Interface, Connector A	QMA Male
Interface, Connector B	QMA Male
Nominal Size	0.240 in
Orientation	0°
Specification Sheet Revision Level	A
Variable Length	For custom lengths contact 1-800-255-1479 (North America), 1-779-435-6500 (International), or an Andrew representative

## Jumper Assembly Sample Label



## Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
700–3000 MHz	1.43	15.00

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant by Exemption
China RoHS SJ/T 11364-2006	Above Maximum Concentration Value (MCV)
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

C240-QMRQMR



POWERED BY



## Included Products

240PQMR-C-CR — QMA Male Right Angle for CNT-240 braided cable

CNT-240 — CNT-240, CNT® 50 Ohm Braided Coaxial Cable, black PE jacket

240PQMR-CA — QMA Male Right Angle for CNT-240 braided cable, for jumpers only not for sale