



C300F-SRTR

CNT-300-FR CNT® Jumper with interface types SMA Male Right Angle and TNC Male Right Angle, variable length

General Specifications

Body Style, Connector A	Right angle
Body Style, Connector B	Right angle
Cable Family	CNT-300
Interface, Connector A	SMA Male
Interface, Connector B	TNC Male
Nominal Size	0.300 in
Orientation	0°
Specification Sheet Revision Level	A
Variable Length	For custom lengths contact 1-800-255-1479 (North America), 1-779-435-6500 (International), or an Andrew representative

Jumper Assembly Sample Label



Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
700–3000 MHz	1.43	15.00

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant by Exemption
China RoHS SJ/T 11364-2006	Above Maximum Concentration Value (MCV)
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

C300F-SRTR

POWERED BY



Included Products

300APSR-C — SMA Male Right Angle for CNT-300 braided cable

300APTR-CR — TNC Male Right Angle for CNT-300 braided cable

CNT-300-FR — CNT-300-FR, CNT® 50 Ohm Braided Coaxial Cable, black non-halogenated, fire retardant polyolefin jacket

CNT-300A-FR — CNT-300-FR, CNT® 50 Ohm Braided Coaxial Cable, black non-halogenated, fire retardant polyolefin jacket