



C400D-DMDM-1M5-X

**CNT-400-DB CNT® Jumper with interface types 7-16 DIN Male and 7-16 DIN Male, 1.5 m**

## General Specifications

|                                    |                    |
|------------------------------------|--------------------|
| Body Style, Connector A            | Straight           |
| Body Style, Connector B            | Straight           |
| Cable Family                       | CNT-400            |
| Interface, Connector A             | 7-16 DIN Male      |
| Interface, Connector B             | 7-16 DIN Male      |
| Nominal Size                       | 0.400 in           |
| Length                             | 1.500 m   4.921 ft |
| Attachment, Connector B            | Field attachment   |
| Specification Sheet Revision Level | A                  |

## Electrical Specifications

|                  |           |
|------------------|-----------|
| DTF, Connector A | -28.00 dB |
| DTF, Connector B | -28.00 dB |

## Jumper Assembly Sample Label



## Regulatory Compliance/Certifications

| Agency        | Classification   |
|---------------|--|
| ISO 9001:2008 | Designed, manufactured and/or distributed under this quality management system |

## Included Products

- CNT-400-DB — CNT-400-DB, CNT® 50 Ohm Braided Coaxial Cable, flooded, black PE jacket
- 400PDM-C — 7-16 DIN Male for CNT-400 braided cable

# Product Specifications

COMMSCOPE®

C400D-DMDM-1M5X



400BPDM-C — 7-16 DIN Male for CNT-400 braided cable