



C400D-DMDM-3M-X  
CNT-400-DB CNT® Jumper with interface types 7-16 DIN Male and 7-16 DIN Male, 3 m

## General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Cable Family	CNT-400
Interface, Connector A	7-16 DIN Male
Interface, Connector B	7-16 DIN Male
Nominal Size	0.400 in
Length	3.000 m   9.843 ft
Attachment, Connector B	Field attachment
Specification Sheet Revision Level	A

## Electrical Specifications

DTF, Connector A	-28.00 dB
DTF, Connector B	-28.00 dB

## Jumper Assembly Sample Label



## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

## Included Products

- CNT-400-DB — CNT-400-DB, CNT® 50 Ohm Braided Coaxial Cable, flooded, black PE jacket
- 400PDM-C — 7-16 DIN Male for CNT-400 braided cable

# Product Specifications

---

COMMScope®

C400D-DMDM-3M-X

POWERED BY



400BPDM-C — 7-16 DIN Male for CNT-400 braided cable