



C400-DMDF-90

CNT-400 CNT® Jumper with interface types 7-16 DIN Male and 7-16 DIN Male, 27.43 m

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Cable Family	CNT-400
Interface, Connector A	7-16 DIN Male
Interface, Connector B	7-16 DIN Male
Nominal Size	0.400 in
Length	27.430 m 89.993 ft
Attachment, Connector B	Field attachment
Specification Sheet Revision Level	A

Jumper Assembly Sample Label



Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
700–3000 MHz	1.43	15.00

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

Included Products

400PDF-C — 7-16 DIN Female for CNT-400 braided cable

CNT-400 — CNT-400, CNT® 50 Ohm Braided Coaxial Cable, variable, black PE jacket

Product Specifications

COMMScope®

C400-DMDF-90



400PDM-C — 7-16 DIN Male for CNT-400 braided cable

400BPDM-C — 7-16 DIN Male for CNT-400 braided cable