



C400F-NMNM-3

CNT-400-FR CNT® Jumper with interface types N Male and N Male, 0.9 m

General Specifications

| | |
|--------------------------------------|--------------------|
| Body Style, Connector A | Straight |
| Body Style, Connector B | Straight |
| Cable Family | CNT-400 |
| Interface, Connector A | N Male |
| Interface, Connector B | N Male |
| Nominal Size | 0.400 in |
| Length | 0.900 m 2.953 ft |
| Attachment, Connector A | Field attachment |
| Attachment, Connector B | Field attachment |
| Specification Sheet Revision Level A | |

Jumper Assembly Sample Label



Return Loss/VSWR

| Frequency Band | VSWR | Return Loss (dB) |
|----------------|------|------------------|
| 700–3000 MHz | 1.29 | 18.00 |

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| ISO 9001:2008 | Designed, manufactured and/or distributed under this quality management system |

Included Products

- CNT-400-FR — CNT-400-FR, CNT® 50 Ohm Braided Coaxial Cable, black non-halogenated, fire retardant polyolefin jacket
- 400APNM-C — Type N Male for CNT-400 braided cable

Product Specifications

COMMScope®

C400F-NMNM-3

POWERED BY



400BPNM-C — Type N Male for CNT-400 braided cable