



C400-NMDR

CNT-400 CNT® Jumper with interface types N Male and 7-16 DIN Male Right Angle, variable length

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Right angle
Cable Family	CNT-400
Interface, Connector A	N Male
Interface, Connector B	7-16 DIN Male
Nominal Size	0.400 in
Attachment, Connector A	Field attachment
Specification Sheet Revision Level	A
Variable Length	For custom lengths contact 1-800-255-1479 (North America), 1-779-435-6500 (International), or an Andrew representative

Jumper Assembly Sample Label



Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
700–3000 MHz	1.43	15.00

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

Included Products

400PDR-CR — 7-16 DIN Male Right Angle for CNT-400 braided cable

CNT-400 — CNT-400, CNT® 50 Ohm Braided Coaxial Cable, variable, black PE jacket

Product Specifications

COMMScope®

C400-NMDR

POWERED BY



400APNM-C — Type N Male for CNT-400 braided cable

400BPNM-C — Type N Male for CNT-400 braided cable