



C400-NMNF-M3
CNT-400 CNT® Jumper with interface types N Male and N Female, 0.3 m

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Cable Family	CNT-400
Interface, Connector A	N Male
Interface, Connector B	N Female
Nominal Size	0.400 in
Length	0.300 m 0.984 ft
Attachment, Connector A	Field attachment
Attachment, Connector B	Field attachment
Specification Sheet Revision Level	A

Jumper Assembly Sample Label



Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
700–3000 MHz	1.29	18.00

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

Included Products

- 400PNF-C — Type N Female for CNT-400 braided cable
- CNT-400 — CNT-400, CNT® 50 Ohm Braided Coaxial Cable, variable, black PE jacket

Product Specifications

COMMScope®

C400-NMNF-M3

POWERED BY



400APNM-C — Type N Male for CNT-400 braided cable

400BPNM-C — Type N Male for CNT-400 braided cable