



C400-NMNM-1M5

CNT-400 CNT® Jumper with interface types N Male and N Male, 1.5 m

## General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Cable Family	CNT-400
Interface, Connector A	N Male
Interface, Connector B	N Male
Nominal Size	0.400 in
Length	1.500 m   4.921 ft
Attachment, Connector A	Field attachment
Attachment, Connector B	Field attachment
Specification Sheet Revision Level	A

## Jumper Assembly Sample Label



## Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
700–3000 MHz	1.29	18.00

## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

## Included Products

CNT-400 — CNT-400, CNT® 50 Ohm Braided Coaxial Cable, variable, black PE jacket

400APNM-C — Type N Male for CNT-400 braided cable

# Product Specifications

COMMSCOPE®

C400-NMNM-1M5



400BPNM-C — Type N Male for CNT-400 braided cable