



C400-NMQM-35

CNT-400 CNT® Jumper with interface types N Male and QMA Male, 10.67 m

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Cable Family	CNT-400
Interface, Connector A	N Male
Interface, Connector B	QMA Male
Nominal Size	0.400 in
Length	10.670 m 35.007 ft
Attachment, Connector A	Field attachment
Specification Sheet Revision Level	A

Jumper Assembly Sample Label



Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
700–3000 MHz	1.43	15.00

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant by Exemption
China RoHS SJ/T 11364-2006	Above Maximum Concentration Value (MCV)
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



C400-NMQM-35

POWERED BY



Included Products

400PQM-CR — QMA Male for CNT-400 braided cable

CNT-400 — CNT-400, CNT® 50 Ohm Braided Coaxial Cable, variable, black PE jacket

400APNM-C — Type N Male for CNT-400 braided cable

400BPNM-C — Type N Male for CNT-400 braided cable