



C400-QMRQMR-35  
CNT-400 CNT® Jumper with interface types QMA Male Right Angle and QMA Male Right Angle, 10.7 m

## General Specifications

Body Style, Connector A	Right angle
Body Style, Connector B	Right angle
Cable Family	CNT-400
Interface, Connector A	QMA Male
Interface, Connector B	QMA Male
Nominal Size	0.400 in
Length	10.700 m   35.105 ft
Orientation	0°
Specification Sheet Revision Level	A

## Jumper Assembly Sample Label



## Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
700–3000 MHz	1.43	15.00

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant by Exemption
China RoHS SJ/T 11364-2006	Above Maximum Concentration Value (MCV)
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



C400-QMRQMR-35

POWERED BY



## Included Products

400PQMR-CR — QMA Male Right Angle for CNT-400 braided cable

CNT-400 — CNT-400, CNT® 50 Ohm Braided Coaxial Cable, variable, black PE jacket