



C600-NMNM-80
CNT-600 CNT® Jumper with interface types N Male and N Male, 24.38 m

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Cable Family	CNT-600
Interface, Connector A	N Male
Interface, Connector B	N Male
Nominal Size	0.600 in
Length	24.380 m 79.987 ft
Attachment, Connector A	Field attachment
Attachment, Connector B	Field attachment
Specification Sheet Revision Level	A

Jumper Assembly Sample Label



Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
700–3000 MHz	1.43	15.00

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant by Exemption
China RoHS SJ/T 11364-2006	Above Maximum Concentration Value (MCV)
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

Product Specifications

COMMScope®

C600-NMNM-80



Included Products

600APNM-C — Type N Male for CNT-600 braided cable

CNT-600 — CNT-600, CNT® 50 Ohm Braided Coaxial Cable, black PE jacket

600BPNM-C — Type N Male for CNT-600 braided cable