



## CA-284090-0016

**RG316/U CNT® Jumper with interface type MCX Male Right Angle, 0.16 m**

### General Specifications

Body Style, Connector A	Right angle
Cable Family	RG316
Interface, Connector A	MCX Male
Interface, Connector B	Sold separately
Length	0.160 m   0.525 ft

### Electrical Specifications

DTF, Connector A	-20.00 dB
------------------	-----------

### Jumper Assembly Sample Label



### Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
700–3000 MHz	1.43	15.00

### Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

### Included Products

100PMR-CR — MCX Male Right Angle for CNT-100 braided cable