

**CKN6103ASP01****FSJ1-50A SureFlex® Jumper with interface types UHF Male and N Male, variable length**

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Cable Family	FSJ1-50A
Interface, Connector A	UHF Male
Interface, Connector B	N Male
Nominal Size	1/4 in
Specification Sheet Revision Level	A
Variable Length	For custom lengths contact 1-800-255-1479 (North America), 1-779-435-6500 (International), or an Andrew representative

Electrical Specifications

DTF, Connector A	-10.00 dB
DTF, Connector B	-28.00 dB

Jumper Assembly Sample Label



Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

Included Products

FSJ1-50A — FSJ1-50A, HELIAX® Superflexible Low Density Foam Coaxial Cable, corrugated copper, 1/4 in, black PE jacket

F1MU — Mini UHF Male for 1/4 in FSJ1-50A cable

CKN6103ASP01



FSJ1RK-50B — FSJ1-50B, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/4 in, black non-halogenated, fire retardant polyolefin jacket