



F1A-PDRDR-30N

**FSJ1-50A SureFlex® Jumper with interface types 7-16 DIN Male Right Angle and 7-16 DIN Male Right Angle, 0.76 m**

## General Specifications

Body Style, Connector A	Right angle
Body Style, Connector B	Right angle
Cable Family	FSJ1-50A
Interface, Connector A	7-16 DIN Male
Interface, Connector B	7-16 DIN Male
Nominal Size	1/4 in
Length	0.760 m   2.493 ft
Orientation	0°
Specification Sheet Revision Level	A

## Jumper Assembly Sample Label



## Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
700–3000 MHz	1.33	17.00

## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

## Included Products

- FSJ1-50A — FSJ1-50A, HELIAX® Superflexible Low Density Foam Coaxial Cable, corrugated copper, 1/4 in, black PE jacket
- FSJ1RK-50B — FSJ1-50B, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/4 in, black non-halogenated,

# Product Specifications

COMMSCOPE®

F1A-PDRDR-30N

fire retardant polyolefin jacket

