

**F1P43A-PNMMN-10M-X****FSJ1P-50A SureFlex® Jumper with interface types N Male and N Male, 10 m**

## General Specifications

|                                    |                      |
|------------------------------------|----------------------|
| Body Style, Connector A            | Straight             |
| Body Style, Connector B            | Straight             |
| Cable Family                       | FSJ1-50A             |
| Interface, Connector A             | N Male               |
| Interface, Connector B             | N Male               |
| Nominal Size                       | 1/4 in               |
| Length                             | 10.000 m   32.808 ft |
| Attachment, Connector B            | Field attachment     |
| Specification Sheet Revision Level | A                    |

## Electrical Specifications

|                  |           |
|------------------|-----------|
| DTF, Connector A | -28.00 dB |
| DTF, Connector B | -28.00 dB |

## Jumper Assembly Sample Label



## Return Loss/VSWR

| Frequency Band | VSWR | Return Loss (dB) |
|----------------|------|------------------|
| 800–970 MHz    | 1.15 | 23.10            |
| 1420–1530 MHz  | 1.15 | 23.10            |
| 1700–2180 MHz  | 1.15 | 23.10            |

## Regulatory Compliance/Certifications

| Agency          | Classification         |
|-----------------|------------------------|
| RoHS 2011/65/EU | Compliant by Exemption |

# Product Specifications

COMMScope®

F1P43A-PNMNM-10M-X

POWERED BY



China RoHS SJ/T 11364-2006  
ISO 9001:2008

Above Maximum Concentration Value (MCV)  
Designed, manufactured and/or distributed under this quality management system



## Included Products

F1TNM-HC — Type N Male for 1/4 in FSJ1-50A cable

F1TQM-HC — QMA Male for 1/4 in FSJ1-50A cable

F1TNM-HC-G — Type N Male for 1/4 in FSJ1-50A cable