



F1P43A-PNMNM-1M-X

FSJ1P-50A SureFlex® Jumper with interface types N Male and N Male, 1 m

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Cable Family	FSJ1-50A
Interface, Connector A	N Male
Interface, Connector B	N Male
Nominal Size	1/4 in
Length	1.000 m 3.281 ft
Attachment, Connector B	Field attachment
Specification Sheet Revision Level	A

Electrical Specifications

DTF, Connector A	-28.00 dB
DTF, Connector B	-28.00 dB

Jumper Assembly Sample Label



Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
800–970 MHz	1.15	23.10
1420–1530 MHz	1.15	23.10
1700–2180 MHz	1.19	21.30

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant by Exemption

Product Specifications

COMMSCOPE®

F1P43A-PNMNM-1M-X



China RoHS SJ/T 11364-2006
ISO 9001:2008

Above Maximum Concentration Value (MCV)
Designed, manufactured and/or distributed under this quality management system



Included Products

F1TNM-HC — Type N Male for 1/4 in FSJ1-50A cable

F1TQM-HC — QMA Male for 1/4 in FSJ1-50A cable

F1TNM-HC-G — Type N Male for 1/4 in FSJ1-50A cable