



F1RNA-PNMNM-1M

FSJ1RK-50B SureFlex® Jumper with interface types N Male and N Male, 1 m

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Cable Family	FSJ1-50B
Interface, Connector A	N Male
Interface, Connector B	N Male
Nominal Size	1/4 in
Length	1.000 m 3.281 ft
Specification Sheet Revision Level	A

Jumper Assembly Sample Label



Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
700–3000 MHz	1.22	20.00

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant by Exemption
China RoHS SJ/T 11364-2006	Above Maximum Concentration Value (MCV)
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

