

**F2A-NMNM-6-P****FSJ2P-50-100 SureFlex® Jumper with interface types N Male and N Male, 6 feet**

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Cable Family	FSJ2-50
Interface, Connector A	N Male
Interface, Connector B	N Male
Nominal Size	3/8 in
Length	1.829 m 6.000 ft
Specification Sheet Revision Level	A

Electrical Specifications

3rd Order IMD	-110.00 dBm
---------------	-------------

Jumper Assembly Sample Label



Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
698–960 MHz	1.08	28.00
1700–2200 MHz	1.08	28.00

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant by Exemption
China RoHS SJ/T 11364-2006	Above Maximum Concentration Value (MCV)
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

Product Specifications

COMMScope®

F2A-NMNM-6P



POWERED BY

