



## F2A-PDMDFPM-2F5

**FSJ2-50 SureFlex® Jumper with interface types 7-16 DIN Male and 7-16 DIN Female Panel Mount, 0.76 m**

### General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Panel mount
Cable Family	FSJ2-50
Interface, Connector A	7-16 DIN Male
Interface, Connector B	7-16 DIN Female
Nominal Size	3/8 in
Length	0.760 m   2.493 ft
Specification Sheet Revision Level	A

### Electrical Specifications

DTF, Connector A	-32.00 dB
DTF, Connector B	-32.00 dB

### Jumper Assembly Sample Label



### Regulatory Compliance/Certifications

#### Agency

RoHS 2011/65/EU  
China RoHS SJ/T 11364-2006  
ISO 9001:2008

#### Classification

Compliant by Exemption  
Above Maximum Concentration Value (MCV)  
Designed, manufactured and/or distributed under this quality management system



# Product Specifications

COMMScope®

F2A-PDMDFPM-2F5

POWERED BY



## Included Products

FSJ2-50 — FSJ2-50, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 3/8 in, black PE jacket