



F2A-PNMNM-10
FSJ2-50 SureFlex® Jumper with interface types N Male and N Male, 3.05 m

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Cable Family	FSJ2-50
Interface, Connector A	N Male
Interface, Connector B	N Male
Nominal Size	3/8 in
Length	3.050 m 10.007 ft
Specification Sheet Revision Level	A

Jumper Assembly Sample Label



Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
700–3000 MHz	1.29	18.00

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant by Exemption
China RoHS SJ/T 11364-2006	Above Maximum Concentration Value (MCV)
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



F2A-PNMM-10

POWERED BY



Included Products

FSJ2-50 — FSJ2-50, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 3/8 in, black PE jacket