

POWERED BY



F2A-PNR

FSJ2-50 SureFlex® Jumper with interface type N Male Right Angle, variable length



General Specifications

Body Style, Connector A	Right angle
Cable Family	FSJ2-50
Interface, Connector A	N Male
Interface, Connector B	Sold separately
Nominal Size	3/8 in
Specification Sheet Revision Level	A
Variable Length	For custom lengths contact 1-800-255-1479 (North America), 1-779-435-6500 (International), or an Andrew representative

Electrical Specifications

DTF, Connector A	-27.00 dB
------------------	-----------

Jumper Assembly Sample Label



Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU
China RoHS SJ/T 11364-2006
ISO 9001:2008

Classification

Compliant by Exemption
Above Maximum Concentration Value (MCV)
Designed, manufactured and/or distributed under this quality management system



Product Specifications

COMMSCOPE®

F2A-PNR



Included Products

FSJ2-50 — FSJ2-50, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 3/8 in, black PE jacket