



F2A-PNRNR

FSJ2-50 SureFlex® Jumper with interface types N Male Right Angle and N Male Right Angle, variable length

General Specifications

Body Style, Connector A	Right angle
Body Style, Connector B	Right angle
Cable Family	FSJ2-50
Interface, Connector A	N Male
Interface, Connector B	N Male
Nominal Size	3/8 in
Orientation	0°
Specification Sheet Revision Level	A
Variable Length	For custom lengths contact 1-800-255-1479 (North America), 1-779-435-6500 (International), or an Andrew representative

Jumper Assembly Sample Label



Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
698–960 MHz	1.1	26.40
1700–2200 MHz	1.1	26.40

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant by Exemption
China RoHS SJ/T 11364-2006	Above Maximum Concentration Value (MCV)
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

Product Specifications

COMMSCOPE®

F2A-PNRNR



Included Products

FSJ2-50 — FSJ2-50, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 3/8 in, black PE jacket