



F4A-BDFDR-1M5

FSJ4-50B SureFlex® Jumper with interface types 7-16 DIN Female Bulkhead and 7-16 DIN Male Right Angle, 1.5 m

General Specifications

Body Style, Connector A	Bulkhead
Body Style, Connector B	Right angle
Cable Family	FSJ4-50B
Interface, Connector A	7-16 DIN Female
Interface, Connector B	7-16 DIN Male
Nominal Size	1/2 in
Length	1.500 m 4.921 ft
Specification Sheet Revision Level	A

Electrical Specifications

DTF, Connector A	-32.00 dB
DTF, Connector B	-32.00 dB

Jumper Assembly Sample Label



Return Loss/VSWR

Frequency Band	VSWR, typical	Return Loss, typical (dB)
0-3000 MHz	1.11	26.00
2.2-2.7 GHz	1.08	28.00

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant by Exemption
China RoHS SJ/T 11364-2006	Above Maximum Concentration Value (MCV)

Product Specifications

COMMScope®

F4A-BDFDR-1M5

POWERED BY



ISO 9001:2008

Designed, manufactured and/or distributed under this quality management system



Included Products

FSJ4-50B — FSJ4-50B, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket