



## F4A-DM-20-P

**FSJ4-50B SureFlex™ Jumper with interface type 7-16 DIN Male, 6.096 m**

### General Specifications

Body Style, Connector A	Straight
Cable Family	FSJ4-50B
Interface, Connector A	7-16 DIN Male
Interface, Connector B	Sold separately
Length	6.096 m   20.000 ft

### Electrical Specifications

3rd Order IMD	-100.00 dBm
DTF, Connector A	-32.00 dB

### Jumper Assembly Sample Label



### Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
698–960 MHz	1.06	30.00
1700–2200 MHz	1.06	30.00

### Included Products

**FSJ4-50B** — FSJ4-50B, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket