



## F4A-DMDM-10-P

**FSJ4-50B SureFlex® Jumper with interface types 7-16 DIN Male and 7-16 DIN Male, 3.048 m**

### General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Cable Family	FSJ4-50B
Interface, Connector A	7-16 DIN Male
Interface, Connector B	7-16 DIN Male
Nominal Size	1/2 in
Length	3.048 m   10.000 ft
Specification Sheet Revision Level	B

### Electrical Specifications

3rd Order IMD	-116.00 dBm
DTF, Connector A	-34.00 dB
DTF, Connector B	-34.00 dB

### Jumper Assembly Sample Label



### Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)	VSWR, typical	Return Loss, typical (dB)
0-3000 MHz			1.11	26.00
698-960 MHz	1.06	30.00		
1700-2200 MHz	1.06	30.00		
2200-2700 MHz	1.11	26.00		

### Regulatory Compliance/Certifications

# Product Specifications

COMMSCOPE®

F4A-DMDM-10-P



**Agency**

ISO 9001:2008

**Classification**

Designed, manufactured and/or distributed under this quality management system

## Included Products

FSJ4-50B — FSJ4-50B, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket