



## F4A-DMDM-25-PX

**FSJ4-50B SureFlex™ Jumper with interface types 7-16 DIN Male and 7-16 DIN Male, 7.620 m**

### General Specifications

|                         |                     |
|-------------------------|---------------------|
| Body Style, Connector A | Straight            |
| Body Style, Connector B | Straight            |
| Cable Family            | FSJ4-50B            |
| Interface, Connector A  | 7-16 DIN Male       |
| Interface, Connector B  | 7-16 DIN Male       |
| Length                  | 7.620 m   25.000 ft |
| Attachment, Connector B | Field attachment    |

### Electrical Specifications

|                  |             |
|------------------|-------------|
| 3rd Order IMD    | -100.00 dBm |
| DTF, Connector A | -32.00 dB   |

### Jumper Assembly Sample Label



### Return Loss/VSWR

| Frequency Band | VSWR | Return Loss (dB) |
|----------------|------|------------------|
| 698–960 MHz    | 1.10 | 26.40            |
| 1700–2200 MHz  | 1.10 | 26.40            |

### Regulatory Compliance/Certifications

| Agency        | Classification   |
|---------------|--|
| ISO 9001:2008 | Designed, manufactured and/or distributed under this quality management system |

### Included Products

FSJ4-50B — FSJ4-50B, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket

F4PDMV2-C — 7-16 DIN Male for 1/2 in FSJ4-50B cable