



F4A-DRDF-PX

FSJ4-50B SureFlex™ Jumper with interface types 7-16 DIN Male Right Angle and 7-16 DIN Female, variable length

General Specifications

Body Style, Connector A	Right angle
Body Style, Connector B	Straight
Cable Family	FSJ4-50B
Interface, Connector A	7-16 DIN Male
Interface, Connector B	7-16 DIN Female
Length	0.000 m 0.000 ft
Attachment, Connector B	Field attachment

Electrical Specifications

3rd Order IMD	-116.00 dBm
DTF, Connector A	-34.00 dB

Jumper Assembly Sample Label



Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
698–960 MHz	1.08	28.00
1700–2200 MHz	1.08	28.00

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

Included Products

FSJ4-50B — FSJ4-50B, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket

F4PDF-C — 7-16 DIN Female for 1/2 in FSJ4-50B cable