



## F4A-NMDM-30-PX

**FSJ4-50B SureFlex™ Jumper with interface types N Male and 7-16 DIN Male, 9.144 m**

### General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Cable Family	FSJ4-50B
Interface, Connector A	N Male
Interface, Connector B	7-16 DIN Male
Length	9.144 m   30.000 ft
Attachment, Connector B	Field attachment

### Electrical Specifications

3rd Order IMD	-100.00 dBm
DTF, Connector A	-32.00 dB

### Jumper Assembly Sample Label



### Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
698–960 MHz	1.10	26.40
1700–2200 MHz	1.10	26.40

### Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

### Included Products

FSJ4-50B — FSJ4-50B, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket

F4PDMV2-C — 7-16 DIN Male for 1/2 in FSJ4-50B cable