



F4A-NMDM-3M-P

FSJ4-50B SureFlex® Jumper with interface types N Male and 7-16 DIN Male, 3 m

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Cable Family	FSJ4-50B
Interface, Connector A	N Male
Interface, Connector B	7-16 DIN Male
Nominal Size	1/2 in
Length	3.000 m 9.843 ft
Specification Sheet Revision Level	B

Electrical Specifications

3rd Order IMD	-112.00 dBm
DTF, Connector A	-34.00 dB
DTF, Connector B	-34.00 dB

Jumper Assembly Sample Label



Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
698–960 MHz	1.06	30.00
1700–2200 MHz	1.06	30.00
2200–2700 MHz	1.11	26.00

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant by Exemption

Product Specifications

COMMScope®

F4A-NMDM-3M-P

POWERED BY



China RoHS SJ/T 11364-2006
ISO 9001:2008

Above Maximum Concentration Value (MCV)
Designed, manufactured and/or distributed under this quality management system



Included Products

FSJ4-50B — FSJ4-50B, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket