



## F4A-NMDM-45-P

**FSJ4-50B SureFlex® Jumper with interface types N Male and 7-16 DIN Male, 13.719 m**

### General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Cable Family	FSJ4-50B
Interface, Connector A	N Male
Interface, Connector B	7-16 DIN Male
Nominal Size	1/2 in
Length	13.719 m   45.010 ft
Specification Sheet Revision Level	B

### Electrical Specifications

3rd Order IMD	-112.00 dBm
DTF, Connector A	-34.00 dB
DTF, Connector B	-34.00 dB

### Jumper Assembly Sample Label



### Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)	VSWR, typical	Return Loss, typical (dB)
0-3000 MHz			1.11	26.00
698-960 MHz	1.10	26.40		
1700-2200 MHz	1.10	26.40		
2200-2700 MHz	1.13	24.00		

### Regulatory Compliance/Certifications

# Product Specifications

COMMScope®

F4A-NMDM-45-P

POWERED BY



**Agency**

ISO 9001:2008

**Classification**

Designed, manufactured and/or distributed under this quality management system

## Included Products

FSJ4-50B — FSJ4-50B, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket