



F4A-NMDM-4-P

FSJ4-50B SureFlex® Jumper with interface types N Male and 7-16 DIN Male, 1.219 m

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Cable Family	FSJ4-50B
Interface, Connector A	N Male
Interface, Connector B	7-16 DIN Male
Nominal Size	1/2 in
Length	1.219 m 3.999 ft
Specification Sheet Revision Level	B

Electrical Specifications

3rd Order IMD	-112.00 dBm
DTF, Connector A	-34.00 dB
DTF, Connector B	-34.00 dB

Jumper Assembly Sample Label



Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)	VSWR, typical	Return Loss, typical (dB)
0-3000 MHz			1.11	26.00
698-960 MHz	1.06	30.00		
1700-2200 MHz	1.06	30.00		
2200-2700 MHz	1.11	26.00		

Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

Product Specifications

COMMSCOPE®

F4A-NMDM-4P

POWERED BY



ISO 9001:2008 Designed, manufactured and/or distributed under this quality management system

Included Products

FSJ4-50B — FSJ4-50B, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket