



F4A-NMDM-6-P
FSJ4-50B SureFlex® Jumper with interface types N Male and 7-16 DIN Male, 2 m

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Cable Family	FSJ4-50B
Interface, Connector A	N Male
Interface, Connector B	7-16 DIN Male
Nominal Size	1/2 in
Length	2.000 m 6.562 ft
Specification Sheet Revision Level	B

Electrical Specifications

3rd Order IMD	-112.00 dBm
DTF, Connector A	-34.00 dB
DTF, Connector B	-34.00 dB

Jumper Assembly Sample Label



Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)	VSWR, typical	Return Loss, typical (dB)
0–3000 MHz			1.11	26.00
698–960 MHz	1.06	30.00		
1700–2200 MHz	1.06	30.00		
2200–2700 MHz	1.11	26.00		

Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

F4A-NMDM-6P

POWERED BY



ISO 9001:2008 Designed, manufactured and/or distributed under this quality management system

Included Products

FSJ4-50B — FSJ4-50B, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket