



F4A-NMNF-6-P

FSJ4-50B SureFlex® Jumper with interface types N Male and N Female, 1.829 m

## General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Cable Family	FSJ4-50B
Interface, Connector A	N Male
Interface, Connector B	N Female
Nominal Size	1/2 in
Length	1.829 m   6.001 ft
Specification Sheet Revision Level	B

## Electrical Specifications

3rd Order IMD	-112.00 dBm
DTF, Connector A	-34.00 dB
DTF, Connector B	-34.00 dB

## Jumper Assembly Sample Label



## Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)	VSWR, typical	Return Loss, typical (dB)
0–3000 MHz			1.11	26.00
698–960 MHz	1.06	30.00		
1700–2200 MHz	1.06	30.00		
2200–2700 MHz	1.11	26.00		

## Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

# Product Specifications

COMMSCOPE®

F4A-NMNF-6-P



ISO 9001:2008    Designed, manufactured and/or distributed under this quality management system

## Included Products

FSJ4-50B — FSJ4-50B, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket