



## F4A-NMNM-40-P

**FSJ4-50B SureFlex™ Jumper with interface types N Male and N Male, 12.192 m**

### Replaced By:

F4A-NMNM-P

FSJ4-50B SureFlex™ Jumper with interface types N Male and N Male, variable length

## General Specifications

|                         |                      |
|-------------------------|----------------------|
| Body Style, Connector A | Straight             |
| Body Style, Connector B | Straight             |
| Cable Family            | FSJ4-50B             |
| Interface, Connector A  | N Male               |
| Interface, Connector B  | N Male               |
| Length                  | 12.192 m   40.000 ft |

## Electrical Specifications

|                  |             |
|------------------|-------------|
| 3rd Order IMD    | -116.00 dBm |
| DTF, Connector A | -34.00 dB   |
| DTF, Connector B | -34.00 dB   |

## Jumper Assembly Sample Label



## Return Loss/VSWR

| Frequency Band | VSWR | Return Loss (dB) |
|----------------|------|------------------|
| 698–960 MHz    | 1.10 | 26.40            |
| 1700–2200 MHz  | 1.10 | 26.40            |

## Regulatory Compliance/Certifications

| Agency        | Classification                                                                 |
|---------------|--------------------------------------------------------------------------------|
| ISO 9001:2008 | Designed, manufactured and/or distributed under this quality management system |

## Included Products

FSJ4-50B — FSJ4-50B, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket