



F4A-NMNM-4-P

FSJ4-50B SureFlex™ Jumper with interface types N Male and N Male, 1.219 m

General Specifications

| | |
|-------------------------|--------------------|
| Body Style, Connector A | Straight |
| Body Style, Connector B | Straight |
| Cable Family | FSJ4-50B |
| Interface, Connector A | N Male |
| Interface, Connector B | N Male |
| Length | 1.219 m 3.999 ft |

Electrical Specifications

| | |
|------------------|-------------|
| 3rd Order IMD | -116.00 dBm |
| DTF, Connector A | -34.00 dB |
| DTF, Connector B | -34.00 dB |

Jumper Assembly Sample Label



Return Loss/VSWR

| Frequency Band | VSWR | Return Loss (dB) |
|----------------|------|------------------|
| 698–960 MHz | 1.06 | 30.00 |
| 1700–2200 MHz | 1.06 | 30.00 |

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| ISO 9001:2008 | Designed, manufactured and/or distributed under this quality management system |

Included Products

FSJ4-50B — FSJ4-50B, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket