



F4A-NR-25-P

FSJ4-50B SureFlex™ Jumper with interface type N Male Right Angle, 7.620 m

General Specifications

Body Style, Connector A	Right angle
Cable Family	FSJ4-50B
Interface, Connector A	N Male
Interface, Connector B	Sold separately
Length	7.620 m 25.000 ft

Electrical Specifications

3rd Order IMD	-116.00 dBm
DTF, Connector A	-34.00 dB

Jumper Assembly Sample Label



Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
698–960 MHz	1.10	26.40
1700–2200 MHz	1.10	26.40

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

Included Products

FSJ4-50B — FSJ4-50B, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket