



## F4A-PDFKM-1M

**FSJ4-50B SureFlex™ Jumper with interface types 7-16 DIN Female and 4.1-9.5 DIN Male, 1 m**

### General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Cable Family	FSJ4-50B
Interface, Connector A	7-16 DIN Female
Interface, Connector B	4.1-9.5 DIN Male
Length	1.000 m   3.281 ft

### Electrical Specifications

DTF, Connector A	-32.00 dB
DTF, Connector B	-32.00 dB

### Jumper Assembly Sample Label



### Regulatory Compliance/Certifications

#### Agency

RoHS 2002/95/EC  
China RoHS SJ/T 11364-2006  
ISO 9001:2008

#### Classification

Compliant by Exemption  
Above Maximum Concentration Value (MCV)  
Designed, manufactured and/or distributed under this quality management system



### Included Products

FSJ4-50B — FSJ4-50B, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket

F4PKM-C — 4.1-9.5 DIN Male for 1/2 in cable