



F4A-PDFKR-1M

FSJ4-50B SureFlex™ Jumper with interface types 7-16 DIN Female and 4.1-9.5 DIN Male Right Angle, 1 m

General Specifications

| | |
|-------------------------|--------------------|
| Body Style, Connector A | Straight |
| Body Style, Connector B | Right angle |
| Cable Family | FSJ4-50B |
| Interface, Connector A | 7-16 DIN Female |
| Interface, Connector B | 4.1-9.5 DIN Male |
| Length | 1.000 m 3.281 ft |

Electrical Specifications

| | |
|------------------|-----------|
| DTF, Connector A | -32.00 dB |
| DTF, Connector B | -32.00 dB |

Jumper Assembly Sample Label



Return Loss/VSWR

| Frequency Band | VSWR | Return Loss (dB) |
|----------------|------|------------------|
| 800–970 MHz | 1.15 | 23.13 |
| 1420–1530 MHz | 1.15 | 23.13 |
| 1700–2180 MHz | 1.15 | 23.13 |

Regulatory Compliance/Certifications

| Agency | Classification |
|----------------------------|--|
| RoHS 2002/95/EC | Compliant by Exemption |
| China RoHS SJ/T 11364-2006 | Above Maximum Concentration Value (MCV) |
| ISO 9001:2008 | Designed, manufactured and/or distributed under this quality management system |



Included Products

FSJ4-50B — FSJ4-50B, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket