



## F4A-PDMDM-1M-S4

**FSJ4-50B SureFlex™ Jumper with interface types 7-16 DIN Male and 7-16 DIN Male, 1 m**

### General Specifications

|                         |                    |
|-------------------------|--------------------|
| Body Style, Connector A | Straight           |
| Body Style, Connector B | Straight           |
| Cable Family            | FSJ4-50B           |
| Interface, Connector A  | 7-16 DIN Male      |
| Interface, Connector B  | 7-16 DIN Male      |
| Length                  | 1.000 m   3.281 ft |

### Electrical Specifications

|                  |             |
|------------------|-------------|
| 3rd Order IMD    | -107.00 dBm |
| DTF, Connector A | -32.00 dB   |
| DTF, Connector B | -32.00 dB   |

### Jumper Assembly Sample Label



### Return Loss/VSWR

| Frequency Band | VSWR | Return Loss (dB) |
|----------------|------|------------------|
| 450–2000 MHz   | 1.11 | 26.00            |

### Regulatory Compliance/Certifications

| Agency                     | Classification                                                                 |
|----------------------------|--------------------------------------------------------------------------------|
| RoHS 2002/95/EC            | Compliant by Exemption                                                         |
| China RoHS SJ/T 11364-2006 | Above Maximum Concentration Value (MCV)                                        |
| ISO 9001:2008              | Designed, manufactured and/or distributed under this quality management system |



### Included Products

FSJ4-50B — FSJ4-50B, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket