



## F4A-PDMDR-6M

**FSJ4-50B SureFlex® Jumper with interface types 7-16 DIN Male and 7-16 DIN Male Right Angle, 6 m**

### General Specifications

|                                    |                     |
|------------------------------------|---------------------|
| Body Style, Connector A            | Straight            |
| Body Style, Connector B            | Right angle         |
| Cable Family                       | FSJ4-50B            |
| Interface, Connector A             | 7-16 DIN Male       |
| Interface, Connector B             | 7-16 DIN Male       |
| Nominal Size                       | 1/2 in              |
| Length                             | 6.000 m   19.685 ft |
| Specification Sheet Revision Level | A                   |

### Electrical Specifications

|                  |           |
|------------------|-----------|
| DTF, Connector A | -32.00 dB |
| DTF, Connector B | -32.00 dB |

### Jumper Assembly Sample Label



### Return Loss/VSWR

| Frequency Band | VSWR, typical | Return Loss, typical (dB) |
|----------------|---------------|---------------------------|
| 0-3000 MHz     | 1.11          | 26.00                     |
| 2.2-2.7 GHz    | 1.08          | 28.00                     |

### Regulatory Compliance/Certifications

| Agency                     | Classification                          |
|----------------------------|-----------------------------------------|
| RoHS 2011/65/EU            | Compliant by Exemption                  |
| China RoHS SJ/T 11364-2006 | Above Maximum Concentration Value (MCV) |

# Product Specifications

COMMScope®

F4A-PDMDR-6M

POWERED BY



ISO 9001:2008

Designed, manufactured and/or distributed under this quality management system



## Included Products

FSJ4-50B — FSJ4-50B, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket